

INSTALLATION REGULATIONS



DESIGN
AWARD
2018




OptiBean (NG) Touch


ANIMO

DEDICATED TO EVERY CUP

INSTALLATION INSTRUCTIONS




- + Dimensions OptiBean (NG) (TOUCH) 409 (W) x 565 (D) x 792 (H), weight approx. 38 kg,
- Dimensions OptiBean 4 (NG) (TOUCH) 455 (W) x 565 (D) x 792 (H), weight approx. 40 kg
- Dimensions OptiBean 4 TS TOUCH 455 (W) x 565 (D) x 865 (H), weight approx. 42 kg
- Dimension worktop minimum 624 (W) x 615 (D) (OB 2,3), 670 (W) x 615 (D) (OB 4)
- left 165 mm space, right 50 mm space, back side minimum 50 mm space



- + Only suitable for indoor installation
- + Place the machine on a firm flat surface, recommended buffet height between 900 and 1050 mm
- + Ambient conditions: humidity max. 80% RH
- + Ambient temperature 10 - 32°C
- ! Fan blows to the rear, refrigerator fan must be clear of any obstructions

INSTALLATION INSTRUCTIONS



WATER SUPPLY

- + According NEN1006
- + Supply pipe: Ø15 mm
- + Water tap, ball valve or otherwise, with aerator and backflow restrictor, due to regulations of the country
- + Water pressure: 2 - 5 Bar (0.2 - 0.5 MPa), if the water pressure is higher, use a reducer
- + Carbonate hardness: 3 - 5 kH 40 - 80 mg/ltr; use a water filter if the hardness is different
- + Total chlorides (Cl) < 50 mg/ ltr
- + pH value 6.5 - 8.5
- ! Placement under the power supply due to the risk of short circuit



POWER SUPPLY

- + According NEN1010
- + 1N ~ 220-240 V / 50-60 Hz,
- + Grounded outlet, separately fused 16 A, within a radius of 1 meter from the machine
- + Power OptiBean: 2275 W
- ! Do not use an extension cable or power strip!
- ! Places above the water supply due to the risk of short circuit



INSTALLATION INSTRUCTIONS

DRAINAGE SUPPLY (optional)


- + According NEN3215
- + PVC minimum Ø32 mm with sphon
- + Transit in buffet minimum Ø60 mm (A)
- ! Top of drain at least 150 mm lower than top of buffet


article number:

03360 LITTER BIN 26 L

1004943 ACCESSORIES FOR LITTER BIN BASE CABINET OPTIBEAN NG

1004945 HOSE KIT DRAINAGE OB NG - 1004474



**WASTE TRANSIT SERVICE**

For the optional waste throughput (B)

- All measurements in mm !
- Drawing is not to scale !