

INSTALLATION REGULATIONS




OptiBean~~X~~


ANIMO

DEDICATED TO EVERY CUP

INSTALLATION INSTRUCTIONS




- + Dimensions OptiBean X 409 (W) x 567 (D) x 780 (H), weight approx. 35 kg
- Dimensions OptiBean X TS 409 (W) x 567 (D) x 870 (H), weight approx. 38 kg
- Dimension worktop minimum 503 (W) x 630 (D)
- left ≥ 170 mm space, right minimum 50 mm space, back side minimum 50 mm space and on top minimum 250 mm space



- + Only suitable for indoor installation
- + Place the machine on a firm flat surface, recommended buffet height between 900 and 1050 mm
- + Ambient conditions: humidity max. 80% RH
- + Ambient temperature 10 - 32°C
- ! Fan blows to the rear

INSTALLATION INSTRUCTIONS



WATER SUPPLY

- + According NEN1006
- + Supply pipe: Ø15 mm
- + Water tap, ball valve or otherwise, with aerator and backflow restrictor, due to regulations of the country
- + Water pressure: 2 - 5 Bar (0,2 - 0,5 MPa), if the water pressure is higher, use a reducer
- + Carbonate hardness: 3 - 5 kH; use a water filter if the hardness is different
- + Total chlorides (Cl) < 50 mg/ ltr
- + pH value 6,5 - 8,5
- ! Placement under the power supply due to the risk of short circuit



POWER SUPPLY

- + According NEN1010
- + 1N ~ 220-240V / 50-60 Hz,
- + Grounded outlet, separately fused 16 A, within a radius of 1 meter from the machine
- + Power OptiBean X: 1.950 W
- ! Do not use an extension cable or power strip!
- ! Places above the water supply due to the risk of short circuit



INSTALLATION INSTRUCTIONS

DRAINAGE SUPPLY (optional)


- + According NEN3215
- + PVC minimum Ø32 mm with sphon
- + Transit in buffet minimum Ø60 mm (A)
- ! Top of drain at least 150 mm lower than top of buffet


article number:

03360 LITTER BIN 26 L

1011063 ACCESSORIES FOR LITTER BIN BASE CABINET OPTIBEAN X (TS)

1011061 DRAIN KIT OPTIBEAN X





WASTE TRANSIT SERVICE

For the optional waste throughput (B)

- All measurements in mm !
- Drawing is not to scale !