


1001276  
 GB NL D F  
 DK NO SE FI



1001367

13897

03329

1001277

1001228

1001276

08165

\*Recommended Spare Part

Type : OPTIBEAN 2 H&C  
 Articulenumber : 1001520

From mach. nr. : 4X 31323  
 Date : 09 - 2015

Page : 1 - 12  
 Rev : 3


Rated voltage : 1N~ 220-240V 50-60Hz 2275W


Drawer : RLF  
 Date : 06-07-11


Spare Parts Info

ANIMO

www.animo.eu



Type : OPTIBEAN 2 H&C Articulenumber : 1001520	From mach. nr. : 4X 31323 Date : 09 - 2015	Page : 2 - 12 Rev : 3	 <a href="http://www.animo.eu">www.animo.eu</a>
Rated voltage : 1N~ 220-240V 50-60Hz 2275W	Drawer : RLF Date : 06-07-11	<h3>Spare Parts Info</h3>	



\*Recommended Spare Part

Type : OPTIBEAN 2 H&C  
 Articulenumber : 1001520

From mach. nr. : 4X 31323  
 Date : 09 - 2015

Page : 3 - 12  
 Rev : 3


Rated voltage : 1N~ 220-240V 50-60Hz 2275W

Drawer : RLF  
 Date : 06-07-11

Spare Parts Info

ANIMO

www.animo.eu



\*Recomended Spare Part

Type : OPTIBEAN 2 H&C  
 Articlenumber : 1001520

From mach. nr. : 4X 31323  
 Date : 09 - 2015

Page : 4 - 12  
 Rev : 3


Rated voltage : 1N~ 220-240V 50-60Hz 2275W

Drawer : RLF  
 Date : 06-07-11

Spare Parts Info

**ANIMO**

www.animo.eu



\*Recomended Spare Part

Type : OPTIBEAN 2 H&C  
 Articulenumber : 1001520

From mach. nr. : 4X 31323  
 Date : 09 - 2015

Page : 5 - 12  
 Rev : 3


Rated voltage : 1N~ 220-240V 50-60Hz 2275W

Drawer : RLF  
 Date : 06-07-11

Spare Parts Info

**ANIMO**

www.animo.eu



\*Recommended Spare Part

Type : OPTIBEAN 2 H&C  
 Articulenumber : 1001520

From mach. nr. : 4X 31323  
 Date : 09 - 2015

Page : 6 - 12  
 Rev : 3

Rated voltage : 1N~ 220-240V 50-60Hz 2275W

Drawer : RLF  
 Date : 06-07-11

Spare Parts Info

ANIMO

www.animo.eu

1001636  
 1002684 \*  
 1001376 \*  
 1001637

1001384 \*  
 1001391 \*

1001387 \*

1001389 \*

1001390 \*

1001388

1001386 \*

06346  
 11x 5 L= 370 mm  
 Silicone

1001378 \*

1001640

1001380 \*

1001379 \*

1001644  
 1001383 \*

1001381 \*

1001377 \*

1001382 \*

1001636

1001967 \* R  
 White

1001968 \* L  
 Grey

Part of Replacement set 25k - 1001395 \*

\*Recomended Spare Part

Type : OPTIBEAN 2 H&C  
 Articulenumber : 1001520

From mach. nr. : 4X 31323  
 Date : 09 - 2015

Page : 7 - 12  
 Rev : 3

Rated voltage : 1N~ 220-240V 50-60Hz 2275W




Drawer : RLF  
 Date : 06-07-11

Spare Parts Info

**ANIMO**

www.animo.eu





\*Recomended Spare Part

Type : OPTIBEAN 2 H&C  
 Articulenumber : 1001520

From mach. nr. : 4X 31323  
 Date : 09 - 2015

Page : 8 - 12  
 Rev : 3

Rated voltage : 1N~ 220-240V 50-60Hz 2275W



Drawer : RLF  
 Date : 06-07-11

Spare Parts Info

**ANIMO**

www.animo.eu





\*Recomended Spare Part

Type : OPTIBEAN 2 H&C  
 Articulenumber : 1001520  
 Rated voltage : 1N~ 220-240V 50-60Hz 2275W


From mach. nr. : 4X 31323  
 Date : 09 - 2015  
 Drawer : RLF  
 Date : 06-07-11

Page : 9 - 12  
 Rev : 3


Spare Parts Info

**ANIMO**  
 www.animo.eu


Accessories




1001372  
Hygiene kit



1001365  
Service kit



1001347  
Hose kit permanently drain



1001395 \*  
Replacement kit 25k

\*Recomended Spare Part

Type : OPTIBEAN 2 H&C  
Articlenumber : 1001520

From mach. nr. : 4X 31323  
Date : 09 - 2015

Page : 10 - 12  
Rev : 3



Rated voltage : 1N~ 220-240V 50-60Hz 2275W

Drawer : RLF  
Date : 06-07-11

Spare Parts Info

**ANIMO**

www.animo.eu



- OptiBean Service kit: 1001365
- Manometer 0...16bar
  - Water measuring cup 2L
  - PTFE tube Ø 8mm for draining boiler & filling descaler


Watermanagement OptiBean  
 - incl. option boiler drain solution  
 - incl. descaling solution boiler & valves  
 - incl. disinfection solution optional cold water system


Animo

PROJECTIE	GETEKEND: MT
	GECONTROLEERD:
	DATUM: 17-09-2010

REV. 4.0	15-09-2015
Changed length of hose in door	
BLAD 1 van 1	TR0496

WATERMANAGEMENT OPTIBEAN



Type : OPTIBEAN 2 H&C	From mach.n.r. : 1V 00001	Page : 1/1	Drawer : J.S.
Artikel : 1001520	Date : 01-2012	Rev. : 1.2	Date : 01-09-2011
Rated voltage: 1N~ 220-240V 50-60Hz 2275W	CIRCUIT DIAGRAM	<b>Animo</b> Premium coffee makers and beverage equipment	Checked : 
			Drawing nr. : <b>S1001520</b>